
DW10

PRODUCT DRAWING



SPECIFICATIONS

Application	Unmanned Surface Vehicle Electric Surfboard, ROV, Etc
Rated Power	540W
Rated Voltage	36V
Maximum Mooring Thrust	≥10kgf
Applicable Water Depth	0-350M
Material Of The Nozzle	POM
Material Of The Shell	Aluminum Alloy
Material Of The Propeller	Aluminum Alloy

Propeller Specifications	ϕ80mm
Main Shaft Sealing Method	Low-Resistance Dynamic Seal
Main Body Structure	Two-Stage Sealing Chamber
Cable Specifications	TPU (Glossy) ϕ8mm-3*16AWG-1.5m
Driver	External
Weight	845g (In Air) / 480g (Underwater)
Environmental Conditions	0-50℃ (Storage) / 0-40℃ (Operation)
Usage Tips	Rinse With Clean Water Promptly After Use

PERFORMANCE CURVES

