


PRODUCT DRAWING



SPECIFICATIONS

Application	Unmanned Surface Vehicle Electric Surfboard, ROV, Etc	Propeller Specifications	φ126mm
Rated Power	910W	Main Shaft Sealing Method	Low-Resistance Dynamic Seal
Rated Voltage	48V	Main Body Structure	Two-Stage Sealing Chamber
Maximum Mooring Thrust	≥20kgf	Cable Specifications	TPU (Matte) φ9mm-3*13AWG-1.5m
Applicable Water Depth	0-350M	Driver	External
Material Of The Nozzle	POM	Weight	1630g (In Air) / 950g (Underwater)
Material Of The Shell	Aluminum Alloy	Environmental Conditions	0-50°C (Storage) / 0-40°C (Operation)
Material Of The Propeller	Aluminum Alloy	Usage Tips	Rinse With Clean Water Promptly After Use

PERFORMANCE CURVES

