


# SW12

## PRODUCT DRAWING



## SPECIFICATIONS

Application	Unmanned Surface Vehicle, Electric Surfboard Handheld Ehruster, Etc	Propeller Specifications	φ106mm
Rated Power	520W	Main Shaft Sealing Method	Low-Resistance Dynamic Seal
Rated Voltage	48V	Main Body Structure	Two-Stage Sealing Chamber
Maximum Mooring Thrust	≥12kgf	Cable Specifications	TPU (Glossy) φ8mm-3*16AWG-1.5m
Applicable Water Depth	0-30M	Driver	External
Material Of The Nozzle	POM	Weight	1180g (In Air) / 640g (Underwater)
Material Of The Shell	Aluminum Alloy	Environmental Conditions	0-50°C (Storage) / 0-40°C (Operation)
Material Of The Propeller	Aluminum Alloy	Usage Tips	Rinse With Clean Water Promptly After Use

## PERFORMANCE CURVES

