


PRODUCT DRAWING



SPECIFICATIONS

Application	Unmanned Surface Vehicle, Electric Surfboard Handheld Ehruster, Etc	Propeller Specifications	$\phi 80$ mm
Rated Power	360W	Main Shaft Sealing Method	Low-Resistance Dynamic Seal
Rated Voltage	36V	Main Body Structure	Two-Stage Sealing Chamber
Maximum Mooring Thrust	≥ 7 kgf	Cable Specifications	TPU (Matte) $\phi 6.5$ mm-3*18AWG-1.5m
Applicable Water Depth	0-30M	Driver	External
Material Of The Nozzle	POM	Weight	700g(In Air) / 395g(underwater)
Material Of The Shell	Aluminum Alloy	Environmental Conditions	0-50°C (Storage) / 0-40°C (Operation)
Material Of The Propeller	Aluminum Alloy	Usage Tips	Rinse With Clean Water Promptly After Use

PERFORMANCE CURVES

